ZenPure

Sample and Vent Valves

The sample and vent valves for high purity piping and stainless steel filter housings are engineered for cleanliness and ease of use. The valves are constructed of 316L stainless steel for excellent resistance to corrosive chemicals and to ensure product purity. They are machined to a <20Ra finish. Each valve comes with it's own serial number, material certificates and certificate of compliance.

The valves come in both in-line and 90 degree models. Additional assemblies come with a pressure gauge, tee fitting and valve for ease of use. The output fitting on the valve is a hose barb to make quick attachments with a hose to vent or take samples. The design of the unit minimizes dead space for possible contamination buildup between usage. The valve has a limited stem travel for safety and valve protection. The knob is made out of Delrin[®], a material from DuPont, which is durable, low wear, low friction plastic, ideal for this application.

The newest release are the inline sampler with a constant flow throw purge. The liquid is pulled from the middle of the stream for sampling. The sample tube is constantly being flushed through by the moving fluid pressure and exiting a small hole on the down stream side right before the Ferrule, NPT or Weld connection to the tubing.

Applications				
Filter Housings	Tanks			
Product Sampling	Product testing			
Pressure Vessels	Day Tanks			



Materials of Construction

Body: 316L Stainless Steel Knob: Solid Delrin Knob USP Class VI Silicone O-Rings:

> FDA Silicon **EPDM**

Viton

Connections

Inlet: Tri-clamp, Ferrule, NPT, Butt Weld

Outlet: 3/8" Hose Barb

Finish

Machined < 20Ra

Operating Conditions

Max operating pressure:

400 psi (27 bar) at 200°F (93°C) 300 psi (20 bar) at 100°F (37°C)





OFSVILF-SSK

OFSVI90F-1



OFSVILF-1-2EXT



OFSVILF-1

ZenPure

Sample and Vent Valves







OFSVILN-1.13EXT



OFSVILN-2EXT



OFSVILN



OFSV90F



OFSVILF-1.13EXT



OFSVILF-2EXT



OFSVILF



OFSV90W



OFSVILW-1.13EXT



OFSVILW-2EXT



OFSVILW





OFSVILF-2-1.13EXT



OFSVILF-2

ZenPure


Sample and Vent Valves

Sample and Vent Valves						
Part number	Connection Type	Connection Size	Configuration Angle	Sampling Stem	Knob Material	
OFSV90N	NPT	1/4"	90 degree	none	Delrin	
OFSVILN-1.13EXT	NPT	1/4"	In-line	1-1/8"	Delrin	
OFSVILN-2EXT	NPT	1/4"	In-line	2"	Delrin	
OFSVILN	NPT	1/4"	In-line	none	Delrin	
OFSV90F-1	Sanitary Ferrule	1"	90 degree	none	Delrin	
OFSVILF-1-1.13EXT	Sanitary Ferrule	1"	In-line	1-1/8"	Delrin	
OFSVILF-1-2EXT	Sanitary Ferrule	1"	In-line	2"	Delrin	
OFSVILF-1	Sanitary Ferrule	1"	In-line	none	Delrin	
OFSV90F	Sanitary Ferrule	1/2"	90 degree	none	Delrin	
OFSVILF-1.13EXT	Sanitary Ferrule	1/2"	In-line	1-1/8"	Delrin	
OFSVILF-2EXT	Sanitary Ferrule	1/2"	In-line	2"	Delrin	
OFSVILF	Sanitary Ferrule	1/2"	In-line	none	Delrin	
OFSVILF-SSK	Sanitary Ferrule	1/2"	In-line	none	Stainless Steel	
OFSV90F-2	Sanitary Ferrule	2"	90 degree	none	Delrin	
OFSVILF-2-1.13EXT	Sanitary Ferrule	2"	In-line	1-1/8"	Delrin	
OFSVILF-2-2EXT	Sanitary Ferrule	2"	In-line	2"	Delrin	
OFSVILF-2	Sanitary Ferrule	2"	In-line	none	Delrin	
OFSV90W	Weld	1/4"	90 degree	none	Delrin	
OFSVILW-1.13EXT	Weld	1/4"	In-line	1-1/8"	Delrin	
OFSVILW-2EXT	Weld	1/4"	In-line	2"	Delrin	
OFSVILW	Weld	1/4"	In-line	none	Delrin	
IGAOFSVILN	NPT	1/4"	Assembly	none	Delrin	
SGAOFSVILF	Sanitary Ferrule	1-1/2"	Assembly	none	Delrin	

Industrial Pressure Gauge and Vent Valve Assembly

Additional Assembly Options

Sanitary Pressure Gauge and Vent Valve Assembly



- × /
 - 100-160 PSI Pressure Gauge
 - 316L Stainless Steel
 - Sanitary Vent/Sample Valve
 - 1 1/2" Electropolished Tri-Clamp Spool
 - (2) Silicone Gaskets & (2) SS Clamps

SANITARY GAUGE GLYCERINE FILLED

SANITARY VALVE

DEPTH SHOP OF THE PROPERTY OF

Your Local Distributor:

ZenPure

North & South Americas: ZenPure Americas, Inc www.zenpure.com Info-us@zenpure.com 703-335-9910 All Other Regions: ZenPure Corporation www.zenpure.com info@zenpure.com +86 571 2288 6800

WIKA MODEL M93X.2A

ZenPure and PureFlo are registered trademarks of ZenPure Corporation or an affiliated company Copyright 2003-2012 ZenPure or an affiliated company. All rights reserved.

Page 359

H77 Rev. 2012.01